

MINIATURE LAMP (7382) Details



Part #	7382				
Description	T1 3/4 BIPIN 14V .08A .3CP				
Bulb Shape	T-1 3/4	Filament	C-2F	Base Style	G-4 Bi-Pin
Glass Diameter (in)	0.22	MOL [†] (in)	0.63	LCL ^{††} (in)	0.50
Glass Diameter (mm)	5.5	MOL (mm)	16.00	LCL (mm)	12.70
Volts	14	MSCP [‡]	0.3	Avg Life Hrs	15000
Watts	1.12	Amps	0.08	RoHS Compliant	

† MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

‡ MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

†† LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.