

KDS824A Deluxe Dispenser

Dispenses low, medium and high viscosity adhesives, liquids and epoxies.

KDS 824A

- Digital timer control allows metered shot repeatability
- Shot time duration adjustable from 0,01 to 99,99 seconds
- Adjustable four position push button timer switch
- Vacuum feature prevents dripping
- Electrically actuated foot pedal
- Accessory port for optional KDS301 vacuum pickup wand or for pressurizing an external cartridge or tank
- Two 0 - 100 PSI regulators and gauges with locking ring
- Benchtop unit for easy reading of dials and adjustment of air pressure and vacuum
- Low voltage unit for safety
- Slide switch easily changes unit from 115 to 230 volts
- Order syringe adapters, kits and other accessories separately



Code-Number: KDS824A



Technical data:

Dimensions L x W x H	197 x 242 x 127 mm
Weight	3.4 kg
Supply voltage	230V / 120V (50 / 60 Hz)
Fuse	0,5 A
Air inlet max.	7 bar
Air outlet	0 - 7 bar
Vacuum	0 - 0,6 bar
Range of adjustments:	0,01 – 99,99 sec.
Adjustment accuracy	+/- 2%
Repeat accuracy	0,0005 sec.
Cycle time	0,12 sec.

Weller Tools GmbH
 Carl-Benz-Str. 2
 74354 Besigheim
 Germany

Phone: +49 (0) 7143 580-0
 Fax.: +49 (0) 7143 580-108
 Email: info@weller-tools.com
 Web: www.weller-tools.com