

Tenma 72-10202 Pinless Moisture Meters

Features
Quickly indicate the moisture content of materials
Depth of penetration about 20-40mm
Low battery indication
MAX/MIN Function
HOLD Function
Auto Power Off
White Backlit LCD Display

Specifications	
Sensor Type	Metal spheroid
Measuring Range	0 to 100 digit
Max Resolution	1
Battery	9V battery
Dimensions	189x 47 x 35mm
Weight	178g

