



Tenma 72-10460

SPECIFICATIONS

Basic Functions	Range	Best Accuracy
Illuminance Measurement(LUX)	20 Lux	$\pm(3.0\%+20)$
	200 Lux	$\pm(3.0\%+8)$
	2000 Lux	$\pm(3.0\%+8)$
	20000 Lux	$\pm(3.0\%+8)$
Illuminance Measurement(FC)	2 FC	$\pm(3.0\%+20)$
	20 FC	$\pm(3.0\%+8)$
	200 FC	$\pm(3.0\%+8)$
	2000 FC	$\pm(3.0\%+8)$
Special Functions		
Display Count		1999
Auto Range		✓
Data Hold		✓
Auto Power Off	Around 10 Minutes	✓
Low Battery Indication	$\leq 7.1V$	✓
MAX Mode		✓
MIN Mode		✓
Data Logging		2044
Auto Record Time Setup		✓
Real-Time Clock		✓
GENERAL CHARACTERISTICS		
Power	9V Alkaline Battery (6LF22)	
LCD Size	22.5 x 32.5mm	
Product Colour	Orange and Grey	
Product Net Weight	185g	
Product Size	195 x 45 x 26mm	
Standard Accessories	Battery, Carrying Bag	
Standard Individual Packing	Gift Box , English Manual	
Standard Quantity Per Carton	40pcs	
Standard Carton Measurement	650 x560 x 300mm(0.11 CBM Per Standard Carton)	
Standard Carton Gross Weight	15kg	