

Black Box Products

Industrial > Cabling & Infrastructure



Bulk Extended-Distance/Quiet Cable— Industrial Environment, PVC Jacket, 4 Conductors (2 Pairs), 2000-ft. (609.6-m)



Send RS-232 data up to 500 feet in noisy environments.

EMN04A-2000

Extended Double Diamond™ Warranty Available
(Lifetime)

Product Highlights

- Low capacitance, braided foil shield.
- 24 AWG stranded construction.
- Guaranteed for life!

Details

Description

Bulk Extended-Distance/Quiet Cable—Industrial Environment, PVC Jacket, 4 Conductors (2 Pairs), 2000-ft. (609.6-m)

Quick Facts

- Low capacitance, braided foil shield.
- 24 AWG stranded construction.
- Guaranteed for life!

Further Details

- Ideal for noisy environments where cable runs are next to power lines and other cabling systems that cause interference.

Tech Spec

Technical Specifications for Bulk Extended-Distance/Quiet Cable—Industrial Environment, PVC Jacket, 4 Conductors (2 Pairs), 2000-ft. (609.6-m):

Cable Type	Twisted pair, PVC jacket
Capacitance	12 pF/ft. ± 2 pF/ft.
Conductor Gauge	24 AWG (7 x 32 AWG) stranded
Resistance	25 ohms/1000 ft.
Shield	One foil and one copper braid

NOTE: Technical specification weight is the unit weight. It is not the packaged shipping weight.