



Product 33871

Number:

Order 57

Abbreviation:

General Miniature Incandescent Lamp Primary For Automotive Applications G4 1/2 Bulb

Description: Shape With Miniature Bayonet Base

Product Information

| | |
|-----------------------------------|-------------------|
| Abbrev. With Packaging Info. | 57 TP 10 |
| Amps (1) | 0.24 |
| Average Rated Life (hr) | 500 |
| Base | Miniature Bayonet |
| Bulb | G4.5 |
| Design Voltage (V) | 14.00 |
| Diameter (in) | 0.59 |
| Diameter (mm) | 15 |
| Filament | C-2V |
| Light Center Length - LCL (in) | 0.5 |
| Light Center Length - LCL (mm) | 12.7 |
| Maximum Overall Length - MOL (in) | 0.84 |
| Maximum Overall Length - MOL (mm) | 21.4 |
| Mean Spherical Candela 1 (MSCD) | 2 |

Footnotes

- Additional product information can be found in the SYLVANIA Automotive, Miniature and Sealed Beam Lamp Catalog Form 208.