

Kit Contents for C425 0201DS Power Inductors

Kit C425A (26 values, 20 of each)

0.5 nH	10%	0201DS-0N5XKEU
0.6 nH	10%	0201DS-0N6XKEU
1.2 nH	5%	0201DS-1N2XJEU
1.3 nH	5%	0201DS-1N3XJEU
1.4 nH	5%	0201DS-1N4XJEU
1.5 nH	5%	0201DS-1N5XJEU
2.2 nH	5%	0201DS-2N2XJEU
2.3 nH	5%	0201DS-2N3XJEU
2.4 nH	5%	0201DS-2N4XJEU
2.5 nH	5%	0201DS-2N5XJEU
3.3 nH	5%	0201DS-3N3XJEU
3.4 nH	5%	0201DS-3N4XJEU
3.5 nH	5%	0201DS-3N5XJEU
3.6 nH	5%	0201DS-3N6XJEU
3.7 nH	5%	0201DS-3N7XJEU
3.8 nH	5%	0201DS-3N8XJEU
3.9 nH	5%	0201DS-3N9XJEU
4.8 nH	5%	0201DS-4N8XJEU
4.9 nH	5%	0201DS-4N9XJEU
5.0 nH	5%	0201DS-5N0XJEU
5.1 nH	5%	0201DS-5N1XJEU
5.2 nH	5%	0201DS-5N2XJEU
5.3 nH	5%	0201DS-5N3XJEU
5.4 nH	5%	0201DS-5N4XJEU
5.5 nH	5%	0201DS-5N5XJEU
6.7 nH	5%	0201DS-6N7XJEU

Kit C425B (26 values, 20 of each)

6.8 nH	5%	0201DS-6N8XJEU
6.9 nH	5%	0201DS-6N9XJEU
7.0 nH	5%	0201DS-7N0XJEU
7.1 nH	5%	0201DS-7N1XJEU
7.2 nH	5%	0201DS-7N2XJEU
7.3 nH	5%	0201DS-7N3XJEU
7.4 nH	5%	0201DS-7N4XJEU
7.5 nH	5%	0201DS-7N5XJEU
7.6 nH	5%	0201DS-7N6XJEU
7.7 nH	5%	0201DS-7N7XJEU
7.8 nH	5%	0201DS-7N8XJEU
7.9 nH	5%	0201DS-7N9XJEU
8.0 nH	5%	0201DS-8N0XJEU
8.1 nH	5%	0201DS-8N1XJEU
8.2 nH	5%	0201DS-8N2XJEU
8.3 nH	5%	0201DS-8N3XJEU
8.4 nH	5%	0201DS-8N4XJEU
8.5 nH	5%	0201DS-8N5XJEU
8.7 nH	5%	0201DS-8N7XJEU
9.0 nH	5%	0201DS-9N0XJEU
9.4 nH	5%	0201DS-9N4XJEU
9.6 nH	5%	0201DS-9N6XJEU
11 nH	5%	0201DS-11NXJEU
12 nH	5%	0201DS-12NXJEU
13 nH	5%	0201DS-13NXJEU
14 nH	5%	0201DS-14NXJEU