

### General Information

Extended Product Type:	416-C6
Product ID:	2CMA193526R1000
EAN:	7392696935265
Catalog Description:	Connector, 6h, 16A, IP44, 3P+N+E
Long Description:	Connector, earthing sleeve position 6h, rated current 16A, IP44 splashproof, 3-poles+neutral+earth, 50 - 60 Hertz, color code red

### Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Connectors

### Ordering

EAN:	7392696935265
Minimum Order Quantity:	10 piece
Country of Origin:	Czech Republic (CZ)

### Dimensions

Product Net Width:	90 mm
Product Net Height:	90 mm
Product Net Length:	154 mm
Product Net Depth:	90 mm
Product Net Weight:	0.225 kg

### Container Information

Package Level 1 Width:	158 mm
Package Level 1 Length:	138 mm
Package Level 1 Height:	345 mm
Package Level 1 Gross Weight:	0.225 kg
Package Level 1 EAN:	7392696935265
Package Level 1 Units:	10 piece

### Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

### Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	<a href="#">2CMC700005D0001;</a>
Environmental Information:	<a href="#">2CMC700001D0002;</a>
RoHS Information:	<a href="#">2CMC700022;</a>

### Additional Information

Additional Information:	Cable entry, compression gland
Cable Cross-Section:	1.0 ... 2.5 mm <sup>2</sup>
Color:	Red
Degree of Protection:	IP44
Enclosure Material:	Polyamide
Frequency (f):	50 Hz 60 Hz
Function:	Connector
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#416-C6
Number of Poles:	5
Object Classification Code:	2CMT005069
Product Main Type:	C
Product Name:	Industrial Connector
Protection Type:	Splashproof
Rated Current (I <sub>n</sub> ):	16 A
Rated Voltage (U <sub>r</sub> ):	346 ... 415 V
RoHS Date:	2009-1
Standards:	IEC 60309-1,-2
Suitable For:	Connectors
Suitable for Product Class:	Industrial Plugs and Sockets

### Classifications

E-nummer:  
UNSPSC:

2416184  
39120000

