



Temperature Probes

Housing Style	Part Number	ID Number	Temperature Range	Length (mm)
Pt100 Temperature Probe, 3/4" Tri-Clamp, Ø8 mm 	TP-104A-TRI3/4-H1141-L03	M9910429	-50° to +120°C (-58° to +248°F)	35
	TP-104A-TRI3/4-H1141-L100	M9910430	-50° to +120°C (-58° to +248°F)	100
Pt100 Temperature Probe, Ø3 mm 	TP-203A-CF-H1141-L050	M9910645	-30° to +350°C (-22° to +662°F)	50
	TP-203A-CF-H1141-L100	M9910402	-30° to +350°C (-22° to +662°F)	100
	TP-203A-CF-H1141-L150	M9910403	-30° to +350°C (-22° to +662°F)	150
	TP-203A-CF-H1141-L200	M9910482	-30° to +350°C (-22° to +662°F)	200
	TP-203A-CF-H1141-L250	M9910404	-30° to +350°C (-22° to +662°F)	250
	TP-203A-CF-H1141-L300	M9910474	-30° to +350°C (-22° to +662°F)	300
	TP-203A-CF-H1141-L1000	M9910496	-30° to +350°C (-22° to +662°F)	1000
	TP-203A-CF-H1141-L2000	M9910499	-30° to +350°C (-22° to +662°F)	2000
Pt100 Temperature Probe, Ø6 mm 	TP-206A-CF-H1141-L050	M9910646	-30° to +350°C (-22° to +662°F)	50
	TP-206A-CF-H1141-L100	M9910475	-30° to +350°C (-22° to +662°F)	100
	TP-206A-CF-H1141-L150	M9910476	-30° to +350°C (-22° to +662°F)	150
	TP-206A-CF-H1141-L200	M9910477	-30° to +350°C (-22° to +662°F)	200
	TP-206A-CF-H1141-L300	M9910478	-30° to +350°C (-22° to +662°F)	300
	TP-206A-CF-H1141-L500	M9910491	-30° to +350°C (-22° to +662°F)	500

Mating cordset for remote connections; RK 4.4T-*RS 4.4T.

* Length in millimeters.

For technical data see pages C15 - C16.

See Section F for additional cordset information.



Temperature Probes

Housing Style	Part Number	ID Number	Temperature Range	Length (m)
Pt100 Cable Probe, 4-Pin M12x1 eurofast®, Ø6 mm 	TP-306A-CF-H1141-L1000	M9910479	-50° to +105°C (-58° to +221°F)	1
	TP-306A-CF-H1141-L2000	M9910480		2
	TP-306A-CF-H1141-L5000	M9910481		5

For technical data see page C16.

Housing Style	Part Number	ID Number	Temperature Range	Length (mm)
PT100 RTD, Threaded Process Connection, 4-pin M12x1 eurofast® 	TP-103A-G1/8-H1141-L013	M9910400	-50° to +120°C (-58° to +248°F)	13
	TP-103A-G1/8-H1141-L024	M9910401		24
PT100 RTD, Threaded Process Connection, 4-pin M12x1 eurofast® 	TP-104A-N1/4-H1141-L005	M9910664	-50° to +120°C (-58° to +248°F)	5
	TP-104A-N1/4-H1141-L035	M9910526		35

For technical data see page C16.

TEMPERATURE