

86 03 125


KNIPEX Mini pliers wrench pliers and a wrench in a single tool




- replaces the need for sets of metric and imperial spanners
- smooth jaws for damage free installation of plated fittings - working directly on chrome!
- adjustable tightening tool
- also excellent for gripping, holding, pressing and bending workpieces
- zero backlash jaw pressure prevents damage to edges of sensitive components
- push the button for adjustment on the workpiece
- parallel jaws give a more solid grip; its design allows flexible adjustment of all widths up to the specified maximum size
- reliable catching of the hinge bolt: no unintentional shifting
- the ratchet type principle allows quick and easy tightening and release of all bolted connections
- lever transmission greater than 10 : 1 for strong gripping power
- Chrome vanadium electric steel, forged, oil-hardened
- the mini pliers wrench for precision mechanics
- particularly suitable for working on small bolted connections
- very good access in very confined areas

The smooth jaws grip all parallel surfaces in the capacity range with a high degree of pressure if necessary and open up almost unlimited application possibilities for the pliers wrench: e.g. for tightening locknuts, exerting pressure to activate the adhesive power of contact adhesives, edge breaking in tile work, snapping cable ties, utilisation as a small vice.

Article No.	86 03 125
EAN	4003773077497
Pliers	nickel plated
Handles	plastic coated
B2 mm	5
B3 mm	9,5
B1 mm	3
Adjustment positions	11
Capacities for nuts Inch	7/8
Capacities for nuts mm	23
Length mm	125
Net weight g	105




Pliers wrench: zero backlash contact pressure, no damage to edges



Conventional open end wrench: edge pressure causes surface damage



Fast adjustment by pushing a button



Working on plated fittings without damage of the surface

technical change and errors excepted