


Datasheet

Art.No. Z7.268.0427.0

Jumper bar IVB WKF 1,5- 4

Cross connector, insulated for DIN rail terminal blocks type WKF..., 4 -pole



Art.No.	Z7.268.0427.0
EAN	4015573732025
Order unit	10 pieces

Approvals

Technical data

General

Colour	Yellow
Type	Cross connector
Modular spacing	4.2 mm
Number of bridged clamps	4
Mounting method	Pluggable
Insulated	Yes

Accessories

Type	Cross connector
Mounting method	Pluggable
Insulated	Yes
Colour	Yellow
Number of bridged clamps	4
Modular spacing	4.2 mm

Drawings

A
1
2
3
4
5
6
7
8
9
10
11
12
13
14
15
16
17
18
19
20
M1
M2
M3
L
G
i
11.1
12.1
1.1

Z7.268.0227.0
 M 1:1

Weitere Daten siehe Katalog
 further data see catalog

Teile-Nr. part-number	Typ type	Polzahl pole	L
Z7.268.0227.0	IVB WKF 1,5- 2	2	7,0
Z7.268.0327.0	IVB WKF 1,5- 3	3	11,2
Z7.268.0427.0	IVB WKF 1,5- 4	4	15,4
Z7.268.0527.0	IVB WKF 1,5- 5	5	19,6
Z7.268.1027.0	IVB WKF 1,5-10	10	40,6
Z7.268.2027.0	IVB WKF 1,5-20	20	82,6

Freifertigkeit nach DIN

Maßstab: 5:1

Werkstoff und Oberflächen:

wieland

Werkstoffbezeichnung

CAD - Zeichnung, keine manuellen Änderungen

2004 Tag Name

Entworfen 09.11. Schmitt J.

Geprüft - -

Normgr. - -

Typ IVB

WKF 1,5-..

1. Verwendung: -

Bl.: 1 von 1

Zeichnung Nr. T Z7.268.0227.0 01K

Ersatz für: -

Benennung

VERBINDUNGSSTECKER

insulated jumper bar

Z7.268.0227.01K_4 DWK028 Schmitt 2004-11-09 10:33:52 1:000