

EURONORD AL 232811



Sample photo

Order symbol: AL 232811
Product nbr: 7011370
Description: Enclosure
Remarks: Aluminium

EAN: 6418074004246
EI. number:
Finland: 3423635
Denmark: 8212004809
Italy: 7321095
Sweden: 2536337
Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with neoprene gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		280	230	110	Ingress Protection (EN 60529): IP 66/67
inch:		11.0	9.1	4.3	Impact Resistance (EN 62262): IK 08
Materials:				NEMA Class: NEMA 1, 4, 4X, 12, 13	
Material:	Aluminium			Certificates:	
Base colour:	RAL 7001			Fimko	
Cover colour:	RAL 7001			Gost R	
Cover screws material:	Stainless steel				
Gasket material:	Neoprene				
Temperatures:					
Short term:	-50 ... 140 °C				
Continuous:	-50 ... 80 °C				
Short term:	-60 ... 285 °F				
Continuous:	-60 ... 175 °F				
Accessories:					
AM 2328	Mounting plate				
ARH 2328	DIN-35 Mounting rail				
MRS 28541	Wall fastening lug (2 pcs)				
PH A & AH A/B	Hinge set				

