

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19204-0003](#)
Status: **Active**
Overview: [Splices](#)
Description: InsulKrimp™ 4 Way Splice for 18-22 AWG Wire

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-19902-009 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#)
[Product Specification PS-19902-013 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family [Splices](#)
Series [19204](#)
Comments 4 Way Connector
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview [Splices](#)
Product Name 4 Way, InsulKrimp™
UPC 800753051577

Physical
Barrel Type Closed
Color - Resin Red
Insulation PVC
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 3.056/g
Packaging Type Bag
Temperature Range - Operating -40°C to +105°C
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 3.68mm max.
Wire Size AWG 18, 20, 22
Wire Size mm² 0.35 - 0.80

Electrical
Voltage - Maximum 600V

Material Info
Old Part Number A-2XCX

Reference - Drawing Numbers
Product Specification PS-19902-009, PS-19902-011, PS-19902-013
Sales Drawing SD-19204-002



Series

image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19204Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
PremiumGrade™	0640010100
Hand Crimp Tool	
Hand Crimp Tool	0640010300
Crimp Head for the	0640050100
AT-200™ Pneumatic	
Hand Tool	
Crimp Head for the	0640050300
AT-200™ Pneumatic	
Hand Tool	