




Performance Plus Duct Tape 8979/8979N

Clean removal for up to 6 months outdoors and indoors




The latest advance in the 3M™ Duct Tape line takes high performance in new directions – outdoors into the sun and cleanly off the surface.

- Removes cleanly for up to six months from most opaque surfaces even after exposure to sunlight and temperature extremes.

- Stays on for up to one year without deterioration even outdoors.
- Saves time of removing sticky residue.
- Strong waterproof backing resists wear, abrasion, moisture, and weathering.
- Aggressive adhesive for quick and reliable attachment.


- High tensile strength for demanding applications.
- Easy to tear straight across and down without curling for ease of application.



Wide variety of outdoor and indoor applications



6 Hanging poly.



7 Outdoor holding.



8 Masking access holes.



9 Sandblast overspray masking.



10 Capping conduit.

3M™ Performance Plus Duct Tape 8979 and 8979N (Nuclear Grade) Physical Properties

Adhesion to steel	52 oz./in. width (57 N/100mm)
Tensile strength	36 lbs./in. (643 N/100mm)
Elongation at break	21%
Tape thickness	12.6 mil (0.33mm)
Temp use range	Up to 200°F (93°C)
Clean removal indoors	40-120°F (4-49°C)
Clean removal outdoors	Up to 6 months
Backing	Polyethylene film over cloth scrim
Adhesive	Natural and synthetic rubber
Compliance	UL723, HUD, BOCA

3M™ Performance Plus Duct Tape Nuclear Grade 8979N Additional Properties

Leachable Halogens: (Cl, Fl, Br)	<200 ppm, MIL-STD-2041D
Leachable Sulfur:	<200 ppm, MIL-STD-2041D
Compliance	ASME NQA-1, MIL-STD-2041D

Note: Data should be considered representative or typical only, and should not be used for specification purposes.

3M™ Performance Plus Duct Tape 8979

UPC	Color	Size**	Rolls/ case	Cases/ pallet
00-048011-53922-5	Slate Blue	24 mm (1")	48	24
*00-021200-56468-0	Slate Blue	48 mm (2")	24	24
00-021200-56469-7	Slate Blue	72 mm (3")	12	30
00-021200-56470-3	Slate Blue	96 mm (4")	12	30
00-048011-58183-5	Slate Blue	144 mm (6")	6	30
*00-048011-53851-8	Slate Blue	48 mm (2")	12**	40
*00-048011-53916-4	Olive	48 mm (2")	24	24
*00-048011-53918-8	Black	48 mm (2")	24	24
00-048011-58120-1	Slate Blue	12"	2	30
00-048011-58119-5	Slate Blue	22"	1	30

3M™ Performance Plus Duct Tape Nuclear Grade 8979N

UPC	Color	Size**	Rolls/ case	Cases/ pallet
00-048011-58130-9	Red	24 mm (1")	48	24
00-048011-53914-0	Red	48 mm (2")	24	24
00-048011-53915-7	Red	72 mm (3")	12	30
00-021200-74327-6	Slate Blue	48 mm (2")	24	24
00-021200-74328-3	Slate Blue	72 mm (3")	12	30
00-048011-58185-9	Slate Blue	144 mm (6")	6	30

* Each roll individually wrapped and marked with UPC Number

** All lengths are 54.8 m (60 yards), except 00-048011-53851-8 which is 22.8 m (25 yards).

Product Use:

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty and Limited Remedy:

3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

Limitation of Liability:

Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Industrial Business
Industrial Adhesives and Tapes Division

900 Bush Avenue, Building 21-1W-10
St. Paul, MN 55144-1000
www.3M.com/duct



The Only NASCAR Officially
Licensed Duct Tape

© 2006, 3M. All rights reserved.
70-0709-5387-5