

Header - SAMPLE PTSM 0,5/ 4-HTB...SMDWH - 1847151


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Pitch: 2.5 mm, Color: white, Assembly: Taped SMD/THT/THR components



Key commercial data

Packing unit	5 pc
GTIN	 4 055626 003122
Weight per Piece (excluding packing)	2.22 g
Custom tariff number	85369010
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Pitch	2.5 mm
Dimension a	7.5 mm

General

Insulating material group	I
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	125 V
Rated voltage (III/2)	160 V
Rated voltage (II/2)	250 V
Nominal current I_N	6 A
Maximum load current	6 A
Insulating material	PA
Inflammability class according to UL 94	V0

Header - SAMPLE PTSM 0,5/ 4-HTB...SMDWH - 1847151

Technical data

General

Color	white
-------	-------


Classifications

eCl@ss

eCl@ss 8.0	27440402
------------	----------

Drawings

Drilling diagram



Dimensioned drawing

