

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130153-0242](#)
Status: **Active**
Overview: [Outlet Boxes](#)
Description: Super-Safeway® Fixed Mount Industrial GFCI, Permanent Mount, Multi Phase, Manual Reset, Flying Leads, 30A, 120/208V 3 Phase, 0.61m (2.0') Lead Length

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	LR6837
UL	E66308

General

Product Family	Power Distribution
Series	130153
Enclosure Rating	NEMA 6P
GFCI Reset	Manual
Mounting Style	Permanent
Open Neutral Relay	Yes
Overview	Outlet Boxes
Product Name	Super-Safeway™
Receptacle Type	N/A
Type	GFCI Industrial Duty, Multi-Phase
UPC	78172542943
Woodhead	Yes

Physical

Cord Diameter	N/A
Cord Grip Body Size	N/A
Cord Length	0.61m (2.0')
Feed-Thru	No
Flip Lid	No
Material - Housing	Nylon
Number of Receptacles	0
Packaging Type	Carton

Electrical

Cord Type	N/A
Current - Maximum per Contact	30A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	N/A
Voltage - Maximum	120V / 208V / 3 Phase

Material Info

Old Part Number	30053-2M5F
-----------------	------------

Reference - Drawing Numbers

Sales Drawing	SD-130153-039
---------------	---------------



EU RoHS

RoHS Compliance

Not Required

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

China RoHS

Search Parts in this Series

[130153Series](#)