

# INTERCONNECTION



## High Temperature Resistant Connection Blocks

- Porcelain body rated to 1000°C
- Inserts rated to 350°C
- 1 to 4 poles available
- 3, 3.5, 4.4 and 6mm insert diameter sizes
- CE marked



### SPECIFICATION

Voltage (max)	450V AC
Working temperature	5°C to 350°C
Insulating body	Porcelain (DIN 40685)
Insert	Nickel-plated brass
Screws	Zinc-plated steel CQ-15



TYPE NO.	POLES	MAX. CURRENT	INSERT DIAMETER	MAX. CONDUCTOR:		LENGTH	WIDTH	HEIGHT	MOUNTING HOLE SIZE:		TERMINAL:	
				RIGID	FLEXIBLE				DIAMETER	SCREW HEAD	PITCH	SCREWS
CHTB4/1N	1	32A	3mm	4mm <sup>2</sup>	4mm <sup>2</sup>	10mm	18mm	17mm	-	-	-	M2.6
CHTB4/2N	2	32A	3mm	4mm <sup>2</sup>	4mm <sup>2</sup>	21.5mm	18mm	17mm	4.5mm	6.9mm	11.5mm	M2.6
CHTB4/3N	3	32A	3mm	4mm <sup>2</sup>	4mm <sup>2</sup>	33mm	18mm	17mm	4.5mm	6.9mm	11.5mm	M2.6
CHTB4/4N	4	32A	3mm	4mm <sup>2</sup>	4mm <sup>2</sup>	44.5mm	18mm	17mm	4.5mm	6.9mm	11.5mm	M2.6
CHTB6/1N	1	41A	3.5mm	6mm <sup>2</sup>	4mm <sup>2</sup>	11mm	20mm	17.5mm	-	-	-	M3
CHTB6/2N	2	41A	3.5mm	6mm <sup>2</sup>	4mm <sup>2</sup>	23.5mm	20mm	17.5mm	4.5mm	7.5mm	12.5mm	M3
CHTB6/3N	3	41A	3.5mm	6mm <sup>2</sup>	4mm <sup>2</sup>	36mm	20mm	17.5mm	4.5mm	7.5mm	12.5mm	M3
CHTB6/4N	4	41A	3.5mm	6mm <sup>2</sup>	4mm <sup>2</sup>	48.5mm	20mm	17.5mm	4.5mm	7.5mm	12.5mm	M3
CHTB10/1N	1	57A	4.4mm	10mm <sup>2</sup>	6mm <sup>2</sup>	12mm	22mm	18mm	-	-	-	M3.5
CHTB10/2N	2	57A	4.4mm	10mm <sup>2</sup>	6mm <sup>2</sup>	26mm	22mm	18mm	5mm	8.5mm	14mm	M3.5
CHTB10/3N	3	57A	4.4mm	10mm <sup>2</sup>	6mm <sup>2</sup>	40mm	22mm	18mm	5mm	8.5mm	14mm	M3.5
CHTB10/4N	4	57A	4.4mm	10mm <sup>2</sup>	6mm <sup>2</sup>	54mm	22mm	18mm	5mm	8.5mm	14mm	M3.5
CHTB16/1N	1	76A	6mm	16mm <sup>2</sup>	10mm <sup>2</sup>	16mm	30mm	23mm	-	-	-	M4
CHTB16/2N	2	76A	6mm	16mm <sup>2</sup>	10mm <sup>2</sup>	34mm	30mm	23mm	5mm	9mm	17.5mm	M4
CHTB16/3N	3	76A	6mm	16mm <sup>2</sup>	10mm <sup>2</sup>	52mm	30mm	23mm	5mm	9mm	17.5mm	M4
CHTB16/4N	4	76A	6mm	16mm <sup>2</sup>	10mm <sup>2</sup>	70mm	30mm	23mm	5mm	9mm	17.5mm	M4

PCB  
TERMINAL  
BLOCKS

INTER-  
CONNECTION

FUSES &  
FUSE-  
HOLDERS

LEDs &  
INDICATORS

MINIATURE  
SWITCHES

LIMIT &  
SAFETY  
SWITCHES

CONTROL  
PRODUCTS

INTERFACE  
MODULES &  
SUPPORTS

RELAY  
BASES

ENCLOSURES

BATTERIES

TRANS-  
FORMERS

