

90° Raintight Corner Pulling Ells

Threaded For Rigid Conduit & IMC

Type FF

90° Female/Female

Use:

Provides a compact wire-pulling point and a 90° change of direction in a conduit run.

Features:


- Threaded for rigid conduit and IMC (NPT)
- Furnished with Neoprene gasketed steel cover, zinc electroplated.
- Raintight

Material/Finish:

Malleable Iron/Zinc Plated

Third Party Certification:

 UL Listed: E-11853

 CSA Certified: 009795


Applicable Third Party Standards:

UL Standard: 514B


CSA Standard: C22.2 No. 18

NEMA: FB-1

Trade Size (inches)	Catalog Number	Dimensions in Inches	
		A	B
1/2	FF-050	1 1/8	1 1/16
3/4	FF-075	2 1/4	1 1/16
1	FF-100	2 3/4	1 15/16
1 1/4	FF-125	3 3/4	2 7/16
1 1/2	FF-150	3 3/4	2 9/16
2	FF-200	4 5/8	3 3/4
2 1/2	FF-250	5 1/2	3 11/16
3	FF-300	6 1/2	3 15/16



Type FF



Type MF

90° Male/Female

Use:

For connecting rigid conduit or IMC to box or enclosures.


Features:

- Threaded for rigid conduit and IMC Female NPT, Male NPSM
- Furnished with neoprene gasketed, steel cover, zinc plated.
- Furnished with locknut.
- Raintight
- Available with insulated throat

Material/Finish:

Malleable Iron/Zinc Electroplated

Third Party Certification:

 UL Listed: E-11853

 CSA Certified: 009795


Applicable Third Party Standards:

UL Standard: 514B

CSA Standard: C22.2 No. 18

NEMA: FB-1

Trade Size (inches)	Catalog Number	Insulated Throat Catalog Number	Dimensions in Inches		
			A	B	C
1/2	MF-050	MF-050T	1 1/8	1 3/8	7/16
3/4	MF-075	MF-075T	2 1/4	1 1/2	1/2
1	MF-100	MF-100T	2 3/4	1 3/4	9/16
1 1/4	MF-125	MF-125T	3 3/4	2 7/8	1 1/16
1 1/2	MF-150	MF-150T	3 3/4	2 1 1/16	1 1/16
2	MF-200	MF-200T	4 5/8	2 13/16	1 3/16
2 1/2	MF-250	MF-250T	5 1/2	3 3/4	1 5/16
3	MF-300	MF-300T	6 1/2	3 15/16	1 1/8



Type MF

