


Female connectors, angled

Identification	No. of contacts	Contact length [mm]		Part number
			termination side	
Type B19 VME, Position P0	95	3.4		17 25 095 1101 17 25 095 2101
Type B19 with upper shield CompactPCI, Position J3 – VME, Position P0	95	3.4		17 25 095 1102 17 25 095 2102
Lower shield for type B19 connectors				17 25 000 4102
Type B22	110	3.4		17 24 110 1101 17 24 110 2101
Type B22 with upper shield CompactPCI, Positions J2, J5	110	3.4		17 24 110 1102 17 24 110 2102
Lower shield for type B22 connectors				17 24 000 4102
Type B25	125	3.4		17 22 125 1101 17 22 125 2101
Type B25 with upper shield	125	3.4		17 22 125 1102 17 22 125 2102
Lower shield for type B25 connectors				17 22 000 4102

harbus
HM

Contact positions	X ₁	X ₂
19	37.9	18 x $\frac{2}{2}$ (= 36)
22	43.9	21 x $\frac{2}{2}$ (= 42)
25	49.9	24 x $\frac{2}{2}$ (= 48)

Dimensions [mm]



Thin print part numbers: performance level 1
Bold print part numbers: performance level 2

* hole on even contact numbers only needed for lower shielding