



Main

Range of product	Harmony XVS
Product or component type	Siren
Device short name	XVS
Colour	White
Signalling type	2 tones siren
[Us] rated supply voltage	120 V AC
Noise level	106 dB (continuous or intermittent tone) at 1 m

Complementary

Material	PC (body)
Product weight	1 kg
Marking	CE
[Uimp] rated impulse withstand voltage	4 kV
Current consumption	80 mA at 120 V
Clamping connection capacity	<= 1 x 1.5 mm ²
Electrical connection	Cable: 6.5...8.5 mm
Width	114 mm
Height	114 mm
Depth	153.2 mm

Environment

Standards	EN/IEC 60947-1 EN/IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-30...50 °C
Class of protection against electric shock	Class II conforming to EN/IEC 61140
IP degree of protection	IP53 conforming to EN/IEC 60529

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0808 - Schneider Electric declaration of conformity

Siren

Dimensions

