



Model 3057
Maintenance/Repair Stool



Model 3000-P



Model 3210C1P
Certified for cleanroom use.



Model 3300-F
Shown with optional footing.



Model 3350E1V



Model 3600-P



Model 3505



Model 3550E-F
Shown with optional footing and casters.



Model 3550-F
Shown with optional footing.



Model 3550C1V
Shown with optional footing and casters.
Certified for cleanroom use.



Model 3555
Certified for cleanroom use.

BEVCO®
 3000 Series
 Backless
 Stools

Office/Industrial
 Laboratory
 Static Control (ESD)
 Cleanroom
 Combination ESD / Cleanroom

SIT-STANDS

Model	Seat Height Adjustment	Seat Type	Base Type	Static Control ESD	Clean Room Rating
3505	22"-32"	Polyurethane	5-star Reinforced Plastic	No	No
3555	20"-30"	Polyurethane	5-star Polished Aluminum	No	Class 10

Includes mushroom glides.

STANDARD STOOLS

Model	Seat Height Adjustment	Seat Type	Base Type	Static Control ESD	Clean Room Rating
3000-P	16"-21"	Polyurethane	5-star Reinforced Plastic	No	No
3300-P	19½"-27"	Polyurethane	5-star Reinforced Plastic	No	No
3500-P	23"-33"	Polyurethane	5-star Reinforced Plastic	No	No
3200-P	19"-24"	Polyurethane	Tubular Steel	No	No
3600-P	24"-29"	Polyurethane	Tubular Steel	No	No
3000-F	17"-22"	Fabric	5-star Reinforced Plastic	No	No
3300-F	20½"-28"	Fabric	5-star Reinforced Plastic	No	No
3500-F	24"-34"	Fabric	5-star Reinforced Plastic	No	No
3200-F	20"-25"	Fabric	Tubular Steel	No	No
3600-F	25"-30"	Fabric	Tubular Steel	No	No
3000-V	17"-22"	Vinyl	5-star Reinforced Plastic	No	No
3300-V	20"-V	Vinyl	5-star Reinforced Plastic	No	No
3500-V	24"-34"	Vinyl	5-star Reinforced Plastic	No	No
3200-V	20"-25"	Vinyl	Tubular Steel	No	No
3600-V	25"-30"	Vinyl	Tubular Steel	No	No

Includes dual wheel casters.

SILVER SERIES STOOLS

Model	Seat Height Adjustment	Seat Type	Base Type	Static Control ESD	Clean Room Rating
3050-P	15½"-20½"	Polyurethane	5-star Polished Aluminum	No	No
3350-P	18½"-26"	Polyurethane	5-star Polished Aluminum	No	No
3550-P	21½"-31½"	Polyurethane	5-star Polished Aluminum	No	No
3210-P	19"-24"	Polyurethane	Chrome Tubular Steel	No	No
3610-P	24"-29"	Polyurethane	Chrome Tubular Steel	No	No
3050-F	16½"-21½"	Fabric	5-star Polished Aluminum	No	No
3350-F	19½"-27"	Fabric	5-star Polished Aluminum	No	No
3550-F	22½"-32½"	Fabric	5-star Polished Aluminum	No	No
3210-F	20"-25"	Fabric	Chrome Tubular Steel	No	No
3610-F	25"-30"	Fabric	Chrome Tubular Steel	No	No
3050-V	16½"-21½"	Vinyl	5-star Polished Aluminum	No	No
3350-V	19½"-27"	Vinyl	5-star Polished Aluminum	No	No
3550-V	22½"-32½"	Vinyl	5-star Polished Aluminum	No	No
3210-V	20"-25"	Vinyl	Chrome Tubular Steel	No	No
3610-V	25"-30"	Vinyl	Chrome Tubular Steel	No	No

Includes dual wheel casters.

STATIC CONTROL (ESD) STOOLS

Model	Seat Height Adjustment	Seat Type	Base Type	Static Control ESD	Clean Room Rating
3050E-F	15½"-20½"	ESD Fabric	5-star Polished Aluminum	Yes	No
3350E-F	18½"-26"	ESD Fabric	5-star Polished Aluminum	Yes	No
3550E-F	21½"-31½"	ESD Fabric	5-star Polished Aluminum	Yes	No
3210E-F	19"-24"	ESD Fabric	Chrome Tubular Steel	Yes	No
3610E-F	24"-29"	ESD Fabric	Chrome Tubular Steel	Yes	No
3050E-V	15½"-20½"	ESD Vinyl	5-star Polished Aluminum	Yes	No
3350E-V	18½"-26"	ESD Vinyl	5-star Polished Aluminum	Yes	No
3550E-V	21½"-31½"	ESD Vinyl	5-star Polished Aluminum	Yes	No
3210E-V	19"-24"	ESD Vinyl	Chrome Tubular Steel	Yes	No
3610E-V	24"-29"	ESD Vinyl	Chrome Tubular Steel	Yes	No

Includes ESD mushroom glides.

CLEAN ROOM STOOLS

Model	Seat Height Adjustment	Seat Type	Base Type	Static Control ESD	Clean Room Rating
3050C1P	14½"-19½"	Polyurethane	5-star Polished Aluminum	No	Class 10
3350C1P	17½"-25"	Polyurethane	5-star Polished Aluminum	No	Class 10
3550C1P	20½"-30½"	Polyurethane	5-star Polished Aluminum	No	Class 10
3210C1P	18"-23"	Polyurethane	Chrome Tubular Steel	No	Class 10
3610C1P	23"-28"	Polyurethane	Chrome Tubular Steel	No	Class 10
3050E1V	15½"-20½"	Vinyl	5-star Polished Aluminum	No	Class 10
3350E1V	18½"-26"	Vinyl	5-star Polished Aluminum	No	Class 10
3550E1V	21½"-31½"	Vinyl	5-star Polished Aluminum	No	Class 10
3210E1V	19"-24"	Vinyl	Chrome Tubular Steel	No	Class 10
3610E1V	24"-29"	Vinyl	Chrome Tubular Steel	No	Class 10

Includes mushroom glides.

COMBINATION CLEANROOM + STATIC CONTROL (ESD) STOOLS

Model	Seat Height Adjustment	Seat Type	Base Type	Static Control ESD	Clean Room Rating
3050E1V	15½"-20½"	ESD Vinyl	5-star Polished Aluminum	Yes	Class 10
3350E1V	18½"-26"	ESD Vinyl	5-star Polished Aluminum	Yes	Class 10
3550E1V	21½"-31½"	ESD Vinyl	5-star Polished Aluminum	Yes	Class 10
3210E1V	19"-24"	ESD Vinyl	Chrome Tubular Steel	Yes	Class 10
3610E1V	24"-29"	ESD Vinyl	Chrome Tubular Steel	Yes	Class 10

Includes ESD mushroom glides.

Standard Features

- Comfortable, durable 15" diameter seat in polyurethane, fabric or vinyl.
- Easy-to-use pneumatic seat height adjustment with 360 degree swivel.
- Sturdy five legged base in tubular steel, polished aluminum or reinforced plastic.
- All models include carpet casters, except as noted.
- ESD models are static dissipative with a resistance of 10⁵ to 10⁹ ohms when measured according to the ANSI/ESD STM12.1-2006 standards.
- All cleanroom stools have been tested to class 10 by an independent laboratory to certify their compliance with Federal Standard 209.

Additional Options

- Stationary mushroom glides for ESD or non ESD applications at no charge.
- Dual wheel hard floor, carpet, interval braking, ESD or non-ESD casters.
- Adjustable chrome footing recommended for stools with seat heights above 19".

BEVCO's complete line of backless stools are built for durability and comfort. Sturdy construction and moderate pricing make these stools ideal for a wide range of applications including general office, medical, laboratory, factory, electronic assembly and clean room. Made in the USA, our products carry BEVCO's superior 12-year guarantee. It's not prorated, works 24 hours a day, and covers any defect in material and workmanship. Pneumatic cylinders are guaranteed for the lifetime of the stool.



MAINTENANCE REPAIR STOOLS

Model	Seat Height Adjustment	Seat Type	Base Type
3057	15½"-20½"	Polyurethane	Tubular Steel
3357	20"-27"	Polyurethane	Tubular Steel

OPTIONS

Part #	Description
CADS/5	Hard floor casters for models with tubular steel bases (set of 5)
3850S/5	Hard floor casters for models with 5-star bases (set of 5)
CARD5	ESD Hard floor casters for models with tubular steel bases (set of 5)
CARD5S	ESD Hard floor casters for models with 5-star bases (set of 5)
CAD5	Carpet casters for models with tubular steel bases (set of 5)
3850/5	Carpet casters for models with 5-star bases (set of 5)
MG	Mushroom Glides
ACF-18	18" Adjustable Footring
ACF-18E	ESD 18" Adjustable Footring

