

REGAL WEALTH ENGINEERING LIMITED

ADD: SUZHOU REPRESENTATIVE OFFICE, 0203A1 1A SINGA PLAZA JINJIHU ROAD SUZHOU INDUSTRIAL PARK, P. R. CHINA

TEL: 86-512-62532393 FAX:86-512-62532690

Type:	5.0mm unbalance microphone cable	Part No. : UBMIC056	
Spec. :	20/0.12BC+PE1.5+SP30/0.12BC+PVC5.0		
Construction:			
Conductor	Construction:	20/0.12mm (BC OFC)	
	DC Resistance(Max. at 20°C):	84.03 Ω /km	
Insulation	Material:	PE	
	Color:	RED	
	Diameter/Thickness:	1.50±0.10mm / 0.44mm±0.10mm	
Filler	Material:	/	
Drain Wire	Construction:	/	
Wrap	Material:	/	
Shield	Construction:	30±2/0.12mm (BC OFC)	
	Coverage:	57%	
	DC Resistance(Max. at 20°C):	61.77 Ω /km	
Jacket	Material:	PVC (S60)	
	Color:	BLACK	
	Diameter/Thickness:	5.0±0.20mm / 1.63±0.10mm	
Marking:	MICROPHONE CABLE		
Performance:			
Physical Properties	Jacket	Swing Test:	≥1500
		Tensile Strength(Mpa):	≥10.5
		Elongation	≥100%
	INSULATION	Swing Test:	/
		Tensile Strength(Mpa):	/
		Elongation	≥150%
Electrical Performance	Capacitance pF/m	130.3	
	Characteristic Impedance(Ω):	38.68	
	RTED TEMPERATURE °C		
	VOITAGE V/DC	60/30	
	Withstand Voltage(KV AC/Min):	0.5	
	Frequency(MHZ)	/	
Attenuation(DB/M)	/		
Drawing:			
			