

OVO5

5.25" design two-way loudspeaker



OVO5 is a 5.25" two-way loudspeaker and without doubt the best value for money design cabinet loudspeaker. Budget and quality sound are united in this elegant low-impedance speaker.

Ideal for paging purposes and quality background music in restaurants, doctors cabinet, classrooms... Its fresh and young design fits into any décor or interior style.

The OVO5 loudspeakers can be mounted with the included wall bracket or can be placed freestanding on a shelf.

The bracket allows flexible positioning, while the sturdy ABS plastic housing guarantees years of trouble free musical enjoyment. Quick-Fit cable clamps ensure quick and easy mounting. Affordable, but by no means a compromise on sound quality –typically Apart!

From 12 pieces on, the OVO5 loudspeakers can be painted into any RAL color (REF: PAINTCAB6).

TECHNICAL SPECIFICATIONS

height in mm	260	width in mm	170
depth in mm	180	loudspeaker system	2-way
woofer size in inch	5,25	woofer cone material	paper
tweeter size in inch	1	mounting system	U-bracket
colour	black / white	impedance in ohms	8
low impedance power in watts	80	SPL 1W/1m in dB	89
max SPL 1m in dB	105	frequency response in Hz	70 - 20K
main construction material	ABS plastic	grille main material	steel
IP rating	40	applicable low impedance	Yes
applicable in 100V	No		

MORE PICTURES

