

**PSEN ma1.4a-52/PSEN ma1.4-10mm/
1unit
Product number:
506323**

Product version:	1.0
Approvals:	CE, cULus Listed, TÜV
Sensor principle:	magnetic
Number of N/O:	2
Connection type:	5m Kabel
Switching voltage:	24 V
Type of switching voltage:	DC
Assured switching distance:	10.0 mm
Assured release distance:	22 mm
Protection type, housing:	IP6K9K
Status indicator:	Without LED
Design:	square
Width dimension:	26.4 mm
Height dimension:	37.0 mm
Depth dimension:	18.0 mm
Gross weight:	203 g
Net weight:	156 g
Ambient temperature:	-10 - 55 °C