



Einhell

GH-EC 2040

This electric chain saw provides excellent performance and perfect robust machining. With ergonomic handle positioning and optimized center of gravity distribution for tireless and safe sawing. The chain is easy to tension and changing without using any tools.

Features

- Big filler opening with quick fastener (1)
- Kickback protection with mechanical instant chain brake (2)
- Sturdy stop claws made of metal (3)
- Tool-free chain tensioning and changing (4)
- High-quality chain from OREGON
- OREGON-cutter rail with sprocket nose
- Chain catch bolt
- Oil tank for automatic chain lubrication with large gauge glass (5)
- Cable strain relief (6)
- High quality **metal gear** for long life (7)

Technical data

■ Mains:	230 – 240 V ~ 50 Hz
■ Power:	2.000 Watt
■ Sword length:	406 mm
■ Cutting length:	375 mm
■ Cutting speed:	13,5 m / s
■ Oil tank volume:	160 ml
■ Product weight:	5.0 kg

Logistic data

■ Net weight:	5.0 kg
■ Gross weight:	5.6 kg
■ Packaging dimensions:	530 x 215 x 275 mm
■ EAN-Code:	4006825 588163
■ Sales unit:	4 pcs

