

Einhell

EXPERT Plus

GE-HC 18 Li T Kit

Cordl. Multifunctional Tool-GT


The cordless multi-functional tool GE-HC 18 Li T Kit is a powerful device to cut higher branches and high hedges from the ground, power network-independently and without effort. Due to the Einhell Power X-Change battery system, the multi-tool has an 18 V rechargeable battery with 3.0 Ah for extensive works. Thereby, the quality blade and chain by OREGON ensure a clean cross section. The automatic chain lubrication and the tool-free change of the chain allow simple operation. The laser-cut and diamond-ground knives of the hedge trimmer provide clean cutting results. The multi-tool can be adapted to any working situation by means of its various adjustment options.

Features

- Battery system - Power X-Change
- Battery capacity control with 3 LEDs
- Battery can be used for other Power-X-Change products
- System high-speed charger included
- 90° pivotable attachment for effortless horizontal cuts
- Motor head tiltable by 7 settings
- Main handle tiltable by 4 settings
- Continuously adjustable telescopic aluminum handle (880-1820 mm)
- Additional adjustable handle with quick fastener
- Metal gearing for a long life
- OREGON quality blade and chain
- Tool less chain tensioning and chain change
- Oil tank for automatic chain lubrication
- Blade made of laser-cut and diamond-grinded steel
- Sturdy bag for storage and transportation

Technical Data

• Voltage d.c.	18 V
• Battery capacity	3000 mAh
• Max. running time	40 min
• Charging time	1h
• Length chain saw bar	200 mm
• Chain cutting speed	3.76 m/s
• Max. cutting length hedge trimmer	400 mm
• Spacing between teeth	16 mm
• Max. cutting thickness	12 mm
• Cuts per minute	1700 min ⁻¹



Logistic Data

- Gross weight export carton 28 kg
- Container quantity (20"/40"/40"HC) 750 | 1551 | 1701



www.tuv.com
ID 1000000000