

RJ45 socket insert - VS-08-BU-RJ45-6-MOD/BU - 1653155

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




RJ45 socket insert, modular (Keystone), CAT6 (Link test), 8-position, shielded, socket on socket



Ethernet

Key commercial data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 970079
Weight per Piece (excluding packing)	8.84 g
Custom tariff number	85366990
Country of origin	Taiwan
Product key	ABNAAF

Technical data

Mechanical characteristics

Number of positions	8
Number of slots	1
Shielded	Yes
Insertion/withdrawal cycles	≥ 750
Connection method	female

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Degree of protection	IP20

Material data

Inflammability class according to UL 94	V0
Contact carrier material	ABS
Contact material	Copper alloy
Contact surface material	Gold over nickel

RJ45 socket insert - VS-08-BU-RJ45-6-MOD/BU - 1653155

Technical data

Electrical characteristics

Number of positions	8
Transmission characteristics (category)	CAT6 Link
Rated current	1.5 A
Pollution degree	2

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260705
eCl@ss 7.0	27440309
eCl@ss 8.0	27440309

ETIM

ETIM 2.0	EC000438
ETIM 3.0	EC000438
ETIM 4.0	EC000438
ETIM 5.0	EC000438

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

RJ45 socket insert - VS-08-BU-RJ45-6-MOD/BU - 1653155

Approvals

Approval details



Accessories

Accessories

Panel mounting frame

Panel mounting frames - VS-08-A-RJ45/MOD-1-IP20 - 1689433



RJ45 panel mounting frame, 1x, IP20, for modular socket inserts (Keystone), without mounting screws

Panel mounting frames - VS-08-A-RJ45/MOD-1-R-IP67 - 1689844



RJ45 panel mounting frame, IP67, for modular socket inserts (Keystone), for round panel cutout, with grommet, with thread and union nut, color: gray

Panel mounting frames - VS-08-A-RJ45/MOD-1-IP67 - 1689080



RJ45 panel mounting frame, IP67, for modular socket inserts (Keystone), for square panel cutout, with grommet, without mounting screws, color: gray

Panel mounting frames - VS-08-A-RJ45/MOD-1-R-IP67 BK - 1658053



RJ45 panel mounting frame, IP67, for modular socket inserts (Keystone), for round panel cutout, with grommet, with thread and union nut, color: black

RJ45 socket insert - VS-08-BU-RJ45-6-MOD/BU - 1653155

Accessories

Panel mounting frames - VS-08-A-RJ45/MOD-1-IP67-BK - 1658642



RJ45 panel mounting frame, IP67, for modular socket inserts (Keystone), for square panel cutout, with grommet, without mounting screws, color: black

Panel mounting frames - VS-08-A-S-RJ45/MOD-1-R-IP67 - 1654772



RJ45 panel mounting frame, IP67, irradiated for welding applications, for modular socket inserts (Keystone), for round panel cutout, with grommet, with thread and union nut


Panel mounting frames - VS-08-A-S-RJ45/MOD-1-IP67 - 1652868




RJ45 panel mounting frame, IP67, irradiated for welding applications, for modular socket inserts (Keystone), for square panel cutout, with grommet, without mounting screws

Drawings

Schematic diagram



Dimensioned drawing



RJ45 socket insert, keystone