


MECHANICAL DETAILS

| | |
|--------------------------|---|
| Shell Style Model | ERA* : Fixed receptacle nut fixing |
| Keying | Circular (can rotate), plug has male contact(s) |
| Housing Material | Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces |
| Cable Fixing | 0 - 0 mm |

Variant 2 :

| | | A | B | E | L | M | S1 |
|-----|--|------|------|------|------|------|------|
| Mm. | | 14 | 16 | 7.5 | 20.2 | 1.5 | 10.5 |
| In. | | 0.55 | 0.63 | 0.30 | 0.80 | 0.06 | 0.41 |



PERFORMANCE DETAIL

| | |
|-----------------------|--------------------------|
| Insert | 1S.250 : 1 Coax (50 Ohm) |
| Insulator | T: PTFE |
| Specifications | |
| Contact Type: | Coaxial 50 Ohm (Solder) |
| Max. Matings: | 1000 |
| Contact Dia.: | 1.6 mm (0.063in) |
| Bucket Dia.: | 1.4 mm (0.055in) |
| Cable type: | A RG |



OTHER CHARACTERISTICS







| | |
|--------------------------|----------------------------|
| Endurance (Shell) | Endurance (Shell): |
| Temp (min) | -55°C |
| Temp (max) | +250°C |
| Humidity (max): | <=95% [at 60 deg C /140 F] |
| Vibration: | 15 g [10 Hz - 2000 Hz] |
| Shock Resistance: | 100 g [6 ms] |
| Salt Spray | >144 hr |
| Climatical | 50/175/21 |
| Shielding (min): | 75 dB (10 MHz) |
| Shielding (min): | 40 dB (1 GHz) |
| IP Rating | 50 |



Available Download

 [Coax_triax_mixed_en.pdf](#)

Related links

-  [Contact](#)
-  [Quote Request](#)
-  [Catalogs Downloads](#)
-  [Catalogs Requests](#)
-  [Sample Request](#)
-  [3D drawings](#)