



HelaTape

HellermannTyton offers a wide range of PVC and rubber tapes for sealing, insulation and bundling of cable and conduits. PVC based tapes are designed for low voltage applications and available in a variety of dimensions and colours. Rubber tapes are best suited for sealing and insulating of cables and splices from low to very high voltage.

Electrical Tapes PVC

- HelaTape Flex 15 - all purpose PVC tape

Features and Benefits

- Insulation tape in several colours
- Highly flexible with good adhesion level
- Flame retardant
- Suitable for mechanical and electrical applications up to 600 volts



One Step to the Web!



Highly flexible and with good adhesion levels HelaTape Flex 15 can be used in several applications.

MATERIAL	Polyvinylchloride (PVC)
Dielectric Strength	40 kV/mm
Adhesion to Steel	2.0 N/10 mm
Adhesion to Backing	1.8 N/10 mm
Elongation at break	200 %
Breaking Strength	24 N/10 mm
Operating Temperature	+90 °C

RoHS

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-FLEX15-15x10	0.15	15.0	10.0 m	Black (BK)	710-00104
	0.15	15.0	10.0 m	Blue (BU)	710-00100
	0.15	15.0	10.0 m	Brown (BN)	710-00107
	0.15	15.0	10.0 m	Green (GN)	710-00103
	0.15	15.0	10.0 m	Green-Yellow (GNYE)	710-00106
	0.15	15.0	10.0 m	Grey (GY)	710-00108
	0.15	15.0	10.0 m	Orange (OG)	710-00110
	0.15	15.0	10.0 m	Red (RD)	710-00101
HTAPE-FLEX15-MX15x10	0.15	15.0	10.0 m	Red (RD), Grey (GY), Yellow (YE), Green (GN), Blue (BU), Orange (OG), White (WH), Brown (BN), Black (BK), Green-Yellow (GNYE)	710-00146
HTAPE-FLEX15-15x10	0.15	15.0	10.0 m	Violet (VT)	710-00109
	0.15	15.0	10.0 m	White (WH)	710-00105
	0.15	15.0	10.0 m	Yellow (YE)	710-00102

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



Electrical Tapes PVC

- HelaTape Flex 15 - all purpose PVC tape

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-FLEX15-15x25	0.15	15.0	25.0 m	Black (BK)	710-00115
	0.15	15.0	25.0 m	Blue (BU)	710-00111
	0.15	15.0	25.0 m	Brown (BN)	710-00118
	0.15	15.0	25.0 m	Green (GN)	710-00114
	0.15	15.0	25.0 m	Green-Yellow (GNYE)	710-00117
	0.15	15.0	25.0 m	Grey (GY)	710-00119
	0.15	15.0	25.0 m	Red (RD)	710-00112
	0.15	15.0	25.0 m	Violet (VT)	710-00120
	0.15	15.0	25.0 m	White (WH)	710-00116
	0.15	15.0	25.0 m	Yellow (YE)	710-00113
HTAPE-FLEX15-19x20	0.15	19.0	20.0 m	Black (BK)	710-00155
	0.15	19.0	20.0 m	Blue (BU)	710-00151
	0.15	19.0	20.0 m	Brown (BN)	710-00158
	0.15	19.0	20.0 m	Green (GN)	710-00154
	0.15	19.0	20.0 m	Green-Yellow (GNYE)	710-00157
	0.15	19.0	20.0 m	Grey (GY)	710-00159
	0.15	19.0	20.0 m	Red (RD)	710-00152
	0.15	19.0	20.0 m	Violet (VT)	710-00160
	0.15	19.0	20.0 m	White (WH)	710-00156
	0.15	19.0	20.0 m	Yellow (YE)	710-00153
HTAPE-FLEX15-25x25	0.15	25.0	25.0 m	Black (BK)	710-00137
	0.15	25.0	25.0 m	Blue (BU)	710-00133
	0.15	25.0	25.0 m	Brown (BN)	710-00140
	0.15	25.0	25.0 m	Green (GN)	710-00136
	0.15	25.0	25.0 m	Green-Yellow (GNYE)	710-00139
	0.15	25.0	25.0 m	Grey (GY)	710-00141
	0.15	25.0	25.0 m	Red (RD)	710-00134
	0.15	25.0	25.0 m	Violet (VT)	710-00142
	0.15	25.0	25.0 m	White (WH)	710-00138
	0.15	25.0	25.0 m	Yellow (YE)	710-00135

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.