



## Value Line V8



- 300 lb. weight capacity
- Pneumatic height adjustment
- Seat foam density: 1 4/5 lb., 36 IFD
- Contoured backrest
- 360° swivel
- 5 leg reinforced plastic base
- Static dissipative with a resistance of 10<sup>5</sup> to 10<sup>9</sup> ohms when measured from the seat or back to the grounding chain
- 3 year warranty
- Made in the USA



Model	Seat Dimensions	Back Dimensions	Seat Height Adjustment	18" Adjustable Chrome Footring	Base Size	Casters or Glides
V800SMG	18"w x 18"d, 2 3/4"	16"w x 15"h, 2"	16" – 21"	No	25"	Mushroom Glides
V800SHC	18"w x 18"d, 2 3/4"	16"w x 15"h, 2"	17" – 22"	No	25"	Hard Floor Casters
V830SMG	18"w x 18"d, 2 3/4"	16"w x 15"h, 2"	20" – 27 1/2"	Yes	27"	Mushroom Glides
V830SHC	18"w x 18"d, 2 3/4"	16"w x 15"h, 2"	21" – 28 1/2"	Yes	27"	Hard Floor Casters
V850SMG	18"w x 18"d, 2 3/4"	16"w x 15"h, 2"	23" – 33"	Yes	27"	Mushroom Glides
V850SHC	18"w x 18"d, 2 3/4"	16"w x 15"h, 2"	24" – 34"	Yes	27"	Hard Floor Casters

### Colors:

Navy Blue Fabric Only