

Capacitor, film, 0.1 uF, +/-20% Tol, -40/+105C, Safety: X1, 760 VAC, Lead Spacing=27.5 mm, Not for new design.



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	31.50	MAX
H	20.50	MAX
T	10.50	MAX
S	27.50	+/-0.4
LL	30.00	+0/-1
F	0.80	NOM

Packaging Specifications	
Package Kind:	Pizza
Package Type:	Tray
Package Quantity:	216

General Information	
Supplier:	KEMET
Dielectric:	Metallized Polypropylene
Application:	Safety: X1
Style:	Radial Box
Approvals:	ENEC,UL,cUL
RoHS:	Yes

Specifications	
Capacitance:	0.1 uF
Voltage:	1500 VDC
Tolerance:	+/-20%
Voltage AC:	760 VAC
Rated Temperature:	105C
Temperature Range:	-40/+105C
Dissipation Factor @ 1 kHz:	0.1%
Dissipation Factor @ 10 kHz:	0.2%
Dissipation Factor @ 100kHz:	0.6%
Insulation Resistance:	30 GOhm
Maximum dVdT:	100 v/us
Miscellaneous Electrical:	Not for new design.