

Han D HMC female contact Au AWG 14



Part number: 09 15 200 6226

Description: Han D HMC female contact Au AWG 14

Features	
Gender:	female
RoHS conformity:	Yes
Type of contact:	Crimp contact
Series:	Han D® HMC
Connection data	
Contact resistance:	≤ 3 mOhm
Wire gauge:	2.5 mm ²
Wire gauge AWG:	AWG 14
Stripping length:	6 mm
Material properties	
Material, contact:	copper alloy
Surface, contacts:	HMC gold plated contacts
Dimensions and weight	
Net Weight:	0.62 g
Norms and specifications	
Specification:	DIN EN 60 664-1DIN EN 61 984
Supplementals	
Diameter of drilling hole:	2.25 mm