



**Wire Joints**  
**T&B Catalog Number:**

**UPC Number:**  
**Status:**  
**Description:**

RC6  
 78621081967  
 Active

Insulated Nylon Wire Joints for Minimum Wire Range 4 (#18) to Maximum Wire Range 2 (#12), White

**WEB\_USE**

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

**Standards**

UL, CSA

**Application**

Provides terminating point for a group of wires running in one direction.

**General**

Insulation Type Insulated Nylon  
 Terminal Series RC  
 Color White  
 Wire Range 4 (#18) - 2 (#12)

**Dimension Information**

Stock Thickness .04  
 A (inches) .43  
 B (inches) .95

**Tooling**

Tool Charts Available on Website  
 Application Tools WT2130A  
 Recommended Tool WT2130A

**Packaging**

T&B Order Multiple 500  
 T&B Inner Pack 500  
 Package in Units 5000  
 Package Type Bulk  
 T&B Sold in UOM Each  
 T&B Weight Per UOM 0.35 lbs. per 100

**Application Support**

Overview Available on Website  
 Wire Guide Tables Available on Website

**Certifications**

RoHS Compliance Yes

**Certifications**



File Nbr:  
 E9809

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)