



Rigid/IMC Conduit Fittings-Hazardous Location T&B Catalog Number:

UPC Number: EXFU-3
Status: 04226934520
Description: Active

1 in. Female to Female Union, Die Cast Aluminum. For hazardous and non-hazardous locations.

Features

- Precision cast and machined surfaces permit safer wire pulling.
- Precision NPT threaded hubs allow trouble-free field installation for rigid or IMC conduit.
- Unique concentric ring design insures critical flame path control

Application

Connecting elements between enclosures, fittings, or boxes which permit future changes to the system in both hazardous and non-hazardous areas.

General

Material Die Cast Aluminum

Dimension Information

Hub Size (inches) 1

Specifications

3dmodel Available on Website

Packaging

T&B Order Multiple 5
T&B Inner Pack 5
Package in Units 25
T&B Sold in UOM Each
T&B Weight Per UOM 0.42 lbs. Each

Notes

- Class I, Div. 1 & 2, Groups C, D - Explosionproof
- Class II, Div. 1, Groups E, F, G - Dust-Ignitionproof
- Class III, Div. 1 & 2 - Raintight
- NEMA 3, 4, 7 CD, 9 EFG - Wet Locations

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E 34438

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321

