



Flexible Braid
T&B Catalog Number:

FBD12-1
 78621010647
 Active

UPC Number:
Status:
Description:

BONDING JUMPER 600AMP 12" LONG

Features

Tin-plated copper braids and ferrules for high conductivity and corrosion resistance.
 Certified C22.2 No. 41 Grounding and Bonding Equipment. Listed UL467 and UL486A for Grounding and Bonding Equipment.

Application

Flexible copper braids for use in substation and grounding applications.

General

Material: Copper
 Finish: Tin-plated

Dimension Information

Bolt Size: 7/16
 Thickness (inches): 0.200
 C (inches): 1.000
 D (inches): 1.30

Specifications

Circular Mil Area: 76,800

Packaging

T&B Inner Pack: 1
 Package in Units: 50
 T&B Sold in UOM: Each
 T&B Weight Per UOM: 37.5 lbs. per 100

Notes

Catalog number is shown in 12 inch length. Standard lengths offered are 6, 12, 18, 24, 30 and 36 inches (end to end). Change the 12 to the desired length.
 The suffix -1 if present after the length indicates 1 bolt hole per ferrule.

Certifications



File Nbr:
 467, 486A

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com