




**SPECIFICATION
CONTROL DRAWING
Crystal Resonator**

FREQUENCY

32.768000kHz



Holder Style	3,2 x 1,5mm
Mode	Fundamental
Adjustment Tolerance	± 20 PPM at 25°C
Operating Temp. Range	-40°C to +85°C
Load Capacitance	12.5 pF
ESR	80000 Ohm
Drive Level	1.0 uW mW
Ageing	+/-5ppm 1st Year Max
Marking	DA**C, D=Facory,A=32.768kHz,** = lot No,C =China

Amdt Date	Change Note	AEL Code
10 MAR 11	Marking Updated	X32K768S113
		Issue Ref C