

# Indicator Lights Neon, LED and Filament Lamp













## Colours and voltages:













-  **Neon** Available with Red, Amber, Green or Clear lenses  
100/130V (marked 110V), 200/250V (marked 230V)
-  **LED - DC** Red, Yellow, Green, Blue, White  
2.0/2.2V Resistors for other voltages available.
-  **LED - AC** Red, Yellow, Green, Blue, White  
110-230V ac operation.
-  **Filament lamp** Available with Red, Amber, Green, Clear or Blue lenses  
6V, 12/14V, 24/28V.

- ▶ Neon, LED, mains LED or filament lamp
- ▶ Bezel sizes from 6.7 to 16.3mm diameter
- ▶ Red, amber, green, blue and clear lenses
- ▶ Red, yellow, green, blue and white LEDs
- ▶ Wide choice of styles

## To create a catalogue number:

Refer to the 2 columns below (terminal and type), then state: Lens colour, voltage and whether neon, LED or filament lamp

TERM	TYPE	PANEL & °C	ILLUM'N OPTIONS	APPROVAL	DIMENSIONS (mm)
L	(L) <b>0569 AW</b> 	9.0 0.8-2.5 Call sales	DC AC	FU, KEUR, SE	
L	(C) <b>0273 00</b> 	9.0	DC	FU, KEUR, SE	
K 2.8		2.0 max	DC	KEUR	
H 4.8		page 6	AC	KEUR, SE	
C 6.3				KEUR	
L	(C) <b>0278 00</b> 	9.0	DC	FU, KEUR, SE	
K 2.8		2.0 max	DC	KEUR	
H 4.8		page 6	AC	KEUR	
C 6.3					
L	(C) <b>0276 AA</b> 	9.5	DC	FU, KEUR, SE	
K 2.8		0.8-2.8	DC	KEUR	
H 4.8		page 6	AC	FU, KEUR, SE	
C 6.3				KEUR	
L	(C) <b>0275 00</b> 	10.0	DC	FU, KEUR, SE	
K 2.8		12.0 max	DC	KEUR	
H 4.8		page 6	AC	KEUR, SE	
C 6.3				KEUR	
L	(C) <b>0275 00</b> Chrome bezel 	10.0	DC	FU, KEUR, SE	
K 2.8		11.5 max	DC	KEUR	
H 4.8		page 6	AC	KEUR, SE	
C 6.3				KEUR	

TERM	TYPE	PANEL & °C	ILLUM'N OPTIONS	APPROVAL	DIMENSIONS (mm)
L K 2.8 H 4.8 C 6.3	(C) <b>0276 00</b> 	10.0 2.8 max page 6	DC AC	KEMA KEMA KEMA	
L K 2.8 H 4.8 C 6.3	(C) <b>0277 00</b> Chrome bezel 	10.0 12.0 max page 6	DC AC	KEMA KEMA KEMA	
L K 2.8 H 4.8 C 6.3	(C) <b>0273 LL</b> 	10.0 0.6-2.0 page 6	DC AC	KEMA KEMA KEMA	For sub-panel mounting, behind a facia. 
L K 2.8 H 4.8 C 6.3	(C) <b>2820 00</b> 	12.0 0.75-2.0 page 6	DC AC	KEMA KEMA KEMA	
L K 2.8 H 4.8 C 6.3	(C) <b>2821 00</b> 	12.0 or 12.7 Ø12.0 = 0.8-2.5 Ø12.7 = 1.1-2.5 page 6	DC AC	KEMA KEMA KEMA	
L K 2.8 H 4.8 C 6.3	(C) <b>0586 00</b> 	12.5 0.8-1.5 page 6	DC AC	KEMA KEMA KEMA	

Indicators

# Indicator Lights Neon, LED and Filament Lamp

Type: (C) 0277 00



## Part Number Ordering

Arcoelectric Part Number	Type	Light Source	Colour	Voltage
C027700FAG	(C) 0277 00	Filament Lamp	Red	24 V
C027700FAH	(C) 0277 00	Filament Lamp	Green	24 V
C027700FAI	(C) 0277 00	Filament Lamp	Amber	24 V
C027700NAO	(C) 0277 00	Neon	Red	230 V
C027700NAP	(C) 0277 00	Neon	Amber	230 V
C027700NAR	(C) 0277 00	Neon	Green	230 V