

Rotating cap
for precise turning and control with fingertip

Precision handle
high quality plastic, cadmium free

Molded on tapered handle
allows rapid rotation

High performance blades
chrome-vanadium-molybdenum steel, Hard chrome finished

Tip
precision ground for exact fit, hard chromed non-slip surface

Wiha Long Life Precision Series



260 Slotted Screwdriver, With Precision Handle [SHOP](#)
Blade high alloy chrome-vanadium-molybdenum steel.

| Item No. | mm | Inch | mm | Inch | mm | Inch | mm | Inch | lbs. | pkg. |
|----------|-----|------|-----|------|------|------|-----|------|------|------|
| 26008 | .80 | 1/32 | 40 | 1.6 | 0.16 | .01 | 120 | 4.7 | .02 | 10 |
| 26010 | 1.0 | .039 | 40 | 1.6 | 0.18 | .01 | 120 | 4.7 | .02 | 10 |
| 26012 | 1.2 | 3/64 | 40 | 1.6 | 0.20 | .01 | 120 | 4.7 | .02 | 10 |
| 26015 | 1.5 | 1/16 | 40 | 1.6 | 0.25 | .01 | 120 | 4.7 | .02 | 10 |
| 26018 | 1.8 | .070 | 40 | 1.6 | 0.30 | .01 | 120 | 4.7 | .02 | 10 |
| 26020 | 2.0 | 5/64 | 40 | 1.6 | 0.40 | .02 | 120 | 4.7 | .02 | 10 |
| 26022 | 2.0 | 5/64 | 50 | 2.0 | 0.40 | .02 | 145 | 5.7 | .02 | 10 |
| 26023 | 2.0 | 5/64 | 100 | 3.9 | 0.40 | .02 | 180 | 7.1 | .03 | 10 |
| 26025 | 2.5 | 3/32 | 50 | 2.0 | 0.40 | .02 | 145 | 5.7 | .03 | 10 |
| 26027 | 2.5 | 3/32 | 100 | 3.9 | 0.40 | .02 | 195 | 7.7 | .03 | 10 |
| 26028 | 2.5 | 3/32 | 150 | 6.0 | 0.40 | .02 | 245 | 9.6 | .04 | 10 |
| 26030 | 3.0 | 1/8 | 50 | 2.0 | 0.50 | .02 | 145 | 5.7 | .03 | 10 |
| 26032 | 3.0 | 1/8 | 60 | 2.4 | 0.50 | .02 | 170 | 6.7 | .04 | 10 |
| 26033 | 3.0 | 1/8 | 100 | 3.9 | 0.50 | .02 | 210 | 8.3 | .04 | 10 |
| 26034 | 3.0 | 1/8 | 150 | 5.9 | 0.50 | .02 | 260 | 10.2 | .05 | 10 |
| 26035 | 3.5 | 9/64 | 60 | 2.4 | 0.60 | .02 | 170 | 6.7 | .05 | 10 |
| 26040 | 4.0 | 5/32 | 60 | 2.4 | 0.80 | .03 | 170 | 6.7 | .05 | 10 |
| 26041 | 4.0 | 5/32 | 100 | 3.9 | 0.80 | .03 | 210 | 8.3 | .06 | 10 |
| 26042 | 4.0 | 5/32 | 150 | 5.9 | 0.80 | .03 | 260 | 10.2 | .07 | 10 |

*Metric dimensions actual - Inch dimensions approximate

Wiha Precision Chip Lifter & Accessories



26810 Precision Chip Lifter [SHOP](#)
Blade chrome-vanadium-molybdenum steel, hardened, chrome-plated. Precision handle high quality plastic, impact resistant.

| Item No. | mm | mm | mm | mm | Inch | lbs. | pkg. |
|----------|----|-----|----|-----|------|------|------|
| 26810 | 1 | 3.5 | 50 | 145 | 5.7 | .07 | 1 |

Standard handle

*Metric dimensions actual - Inch dimensions approximate



26001 Pocket Clip for Precision Screwdrivers [SHOP](#)
Tool clips turn Precision Screwdrivers into Pocket Screwdrivers.

| Item No. | lbs. | pkg. |
|----------|----------------------------|---------|
| 26001 | Fits all Precision handles | .0035 1 |



26000 Plastic Precision Tool Rack [SHOP](#)
Rack holds 6 precision screwdrivers, can be set on workbench. Also has holes for hanging. Made from high quality plastic.

| Item No. | lbs. | pkg. |
|----------|-----------------------------------|-------|
| 26000 | Rack for 6 Precision screwdrivers | .08 1 |

26090 6 Piece Precision Slotted Set [SHOP](#)
Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished.

| Item No. | Slotted: | lbs. |
|----------|-----------------|------|
| 26090 | 1.5, 2.0 x 40mm | .27 |
| | 2.5, 3.0 x 50mm | |
| | 3.5, 4.0 x 60mm | |



26099 8 Piece Precision Slotted Set [SHOP](#)
Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. In canvas storage pouch

| Item No. | Slotted: | lbs. |
|----------|----------------------------------|------|
| 26099 | 1.0, 1.2, 1.5, 2.0 x 40mm | .54 |
| | 2.5, 3.0 x 50mm, 3.5, 4.0 x 60mm | |