

CONTROL PRODUCTS

Piezo switches, Point Illuminated

Aluminium piezo switches offering rugged, sealed tamper and vandal resistant solid state switching. Exceptional durability and reliability.

- Red/green spot illumination
- 28mm diameter actuator
- 22.5mm diameter mounting hole (PG16)
- Normally open, momentary action
- Make impulse time of 125-300 msec
- Choice of flat and recessed actuator
- Wire termination
- IP68 Sealed

SPECIFICATIONS

| | |
|-----------------------|-----------------------|
| Operating voltage | 1-24V AC/DC |
| Switching current | 0.2A max |
| Actuation force | 3-5N |
| Operating temperature | from -40°C to +125°C |
| Ingress Protection | IP68 |
| Lifetime | 50 million operations |
| 'ON' resistance | <20Ω |
| 'OFF' resistance | >5mΩ |

CPS22IF-ALNA-24RG



CPS22IR-ALNA-24RG



| PART NO. | DESCRIPTION |
|-------------------|-------------|
| CPS22IF-ALNA-24RG | Flush |
| CPS22IR-ALNA-24RG | Recessed |

