

Mountable 4 Port Rugged Industrial USB Hub

StarTech ID: ST4200USBM



This sturdy, industrial grade USB hub can be wall mounted or installed onto a DIN rail for convenient access to its 4 female USB ports, providing a work area, server room, or industrial area with USB 2.0 connectivity.

With support for Hi-Speed USB 2.0 data transfer rates of up to 480 Mbps, this 4 port USB hub is backwards compatible with USB 1.1 specifications and can be powered through the host USB bus, or self powered using a three wire terminal block connector (7-24V).

Applications

- Locations where a USB hub needs to be securely mounted to a surface, such as a wall or under a desk
- Environments subject to large temperature variances or where physical damage may occur, such as within a factory

Features

- High Speed USB 2.0 compliant, supporting transfer rates up to 480 Mbps
- Support for multiple mounting methods (Wall/Surface mount and DIN rail)
- All metal construction
- Optional external power connector
- Includes 2 meter USB host cable

Technical Specifications

Warranty	2 Years
Ports	4
Interface	USB 2.0
Industry Standards	USB 2.0
External Ports	1 - Terminal Block (3 Wire)
External Ports	1 - USB B (4 pin) Female
External Ports	4 - USB A (4 pin) Female
Maximum Data Transfer Rate	480 Mbps
MTBF	193,317.8 Hours
OS Compatibility	OS independent; No software or drivers required
System and Cable Requirements	Any computer with a USB 2.0 port
Color	Black
Enclosure Type	Steel
Product Length	114.5 mm [4.5 in]
Product Width	57.3 mm [2.3 in]
Product Height	26.3 mm [1 in]
Product Weight	410 g [14.5 oz]
LED Indicators	1 - Power
Power Source	Terminal Block
Input Voltage	7 ~ 24 DC
Operating Temperature	0°C to 55°C (32°F to 131°F)
Storage Temperature	-20°C to 85°C (-4°F to 185°F)
Shipping (Package) Weight	0.4 kg [0.9 lb]
Included in Package	1 - USB Cable
Included in Package	1 - DIN Mounting Rails
Included in Package	1 - USB 2.0 Hub
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility



Operating System
Independent

 **RoHS Compliant**
Available