HAND HELD CASES

UNIVERSAL ENCLOSURES

HAND HELD CASES

HEAVY DUTY ENCLOSURES

DIN RAIL BOXES

INTERFACE SUPPORTS

CONTROL STATIONS

DIECAST & METAL BOXES

DESKTOP & INSTRUMENT CASES

POTTING BOXES

19" ENCLOSURES

19" CABINETS

DEVELOPMENT BOARD ENCLOSURES

CUSTOM SIZED ENCLOSURES

CUSTOM SERVICES

62 Series Pock Boxes


Contemporary range of small robust hand-held boxes with bevelled and rounded edges.

- Moulded in high impact ABS
- Snap-fit assembly
- Recesses in lid and base for membrane keypads or overlays
- Excellent properties for machining
- Key-ring lug style available
- Optional EPDM gasket for IP65 seal

SPECIFICATION			
Material	Lid and base high impact ABS		
Operating Temperature	Resistant to temperatures of up to 85°C		
Protection class	IP62 as standard		
	IP65 with gasket option		
Standard colours	Light grey similar to RAL 7035		
	Black similar to RAL 9004		
Standard unit includes	Lid & base		
Options	IP65 gasket		

BLACK	LIGHT GREY	LENGTH	WIDTH	HEIGHT	STYLE
CHH621BLK	CHH621GRY	55mm	40mm	18mm	-
CHH622BLK	CHH622GRY	60mm	40mm	18mm	key ring lug
CHH623BLK	CHH623GRY	70mm	50mm	20mm	_





62-IP Gasket

- EPDM rubber gasket
- IP65 protection
- Operating temperature -20°C to +85°C









+44 (0)1638 716101