

1000W 230V AVR Line Conditioner, Power Conditioner, AC Surge Protector, 4 Outlets, Uniplug Adapter

MODEL NUMBER: LR1000



Description

Tripp Lite's LR1000 automatic voltage regulation system offers complete protection from brownouts, overvoltages and transient surges for computers, printers, fax machines and more. Transformer-based voltage correction circuits maintain usable 220-240V nominal AC output during brownouts as low as 168V and overvoltages to 278V. Network grade equipment protection offers AC surge and noise suppression. Supports heavy loads up to 1000 watts. Includes 4 protected outlets (2 x 5-15R; 2 x C13), 2m-line cord and 7 diagnostic LEDs that display incoming voltage level, surge protection status and line fault conditions.

Features

- Maintains usable 220-240V nominal output during brownouts as low as 168V and overvoltages as high as 278V
- 1000 watts output power rating supports heavy 220-240V loads up to 4 amps
- Network grade surge suppression
- EMI/RFI noise filtering
- 3 diagnostic LEDs indicate input voltage levels
- 2 protected NEMA5-15R and 2 C13 outlets
- 2m detachable AC power cord with standard NEMA5-15P input plug

Specifications

| OUTPUT | |
|-------------------------------------|--------------------|
| Nominal Output Voltage(s) Supported | 230V |
| Output Receptacles | (2) 5-15R; (2) C13 |

Highlights

- Automatically adjusts low or high voltage without the aid of a battery
- 1000 watts continuous
- 2 NEMA 5-15R and 2 C13 outlets
- Includes a uniplug adapter

Applications

- Maintains usable output voltage during severe brownouts and overvoltages for printers, fax machines, computers, audio/video equipment, CAD/CAM/CAE workstations, network nodes, file servers, phone systems, point-of-sale terminals, and other applications requiring steady input power.

Package Includes

- LR1000 Line Conditioner
- UNIPLUG Plug Adapter
- International Ground Pin Adapter
- Optional 2m C13-to-NEMA 5-15P input cord
- Instruction manual and warranty information



| | |
|---|---|
| Output (Watts) | 1000 |
| Outlet Details | Includes 1 uniplug adapter that converts one of the built-in outlets to accept a variety of country specific plug types |
| INPUT | |
| Input Cord Length (ft.) | 6 |
| Input Cord Length (m) | 1.83 |
| LEDS ALARMS & SWITCHES | |
| Front Panel LEDs | 3 LEDs show incoming voltage status |
| SURGE / NOISE SUPPRESSION | |
| EMI / RFI AC Noise Suppression | 75 dB |
| AC Suppression Joule Rating | 1200 |
| PHYSICAL | |
| Shipping Weight (lbs.) | 9.00 |
| Shipping Weight (kg) | 4.08 |
| Unit Dimensions (hwd / in.) | 7 x 6 x 7 |
| Unit Dimensions (hwd / cm) | 17.8 x 15.2 x 17.8 |
| Material of Construction | Plastic |
| Form Factors Supported | Box-shaped power tap format |
| WARRANTY | |
| Product Warranty Period (International) | 2-year limited warranty |
| Product Warranty Period (Mexico) | 2-year limited warranty |
| Product Warranty Period (Puerto Rico) | 2-year limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.