

# INA-67-S

Optical USB  
3-button mouse



Desktop &  
Servers



Notebooks &  
Mac's



Tablet &  
Smartphones



Raspberry Pi &  
Android MiniPC

The ideal USB optical mouse for all your devices

Looking for a low priced optical mouse but need quality and performance?

The new **INA-67-S** from LMS Data is a new, low cost 1000 dpi LED optical tracking mouse offering enhanced and super-smooth tracking on almost any surface. Around 20% better resolution than our existing INA-67 but still retaining the comfortable 3/4 size form factor and of course 3-button design complete with central scroll wheel.

Ideal for general computer usage, but also ideal for business, education and mobile users, the **INA-67-S** is ideal for all platforms, Windows8(tm), Mac OS X(tm) and the new breed of Android(tm) smartphones and tablet computers which feature a USB port, or, with the inclusion of a USB OTG (on-the-go) adapter which fits into any microUSB port.

So if your looking for a low cost but performance mouse then look no further than the new LMS Data **INA-67-S**.

## specifications:

Optical 1000 dpi resolution tracking on most surfaces

3-button control with scroll-wheel function

Plug n' play USB connectivity with generous cable length

3/4 size design - ideal for both adults and junior users

Ideal for business, education, mobile users and casual gamers

Ideal for Windows(tm), Mac(tm), Linux(tm), PI(tm) users

Ideal for Android(tm) smartphone and tablet users\*

Retail display box design

\* Android(tm) device must have USB port, such as OTG adapter



USB OTG conversion  
adapter for Android(tm)



**C-USBF-MI**



Copyright 2013 LMS Data  
All trademarks acknowledged E&OE.  
Details subject to change