

# R95-105





## 11-Pin Heavy Duty Square Base Socket

### Features

- Panel/Surface Mount
- Pressure Clamp Screws
- Accepts .187" Blade Terminals
- Hold down clip supplied with socket, also available separately (R95-002)

### Electrical Rating:

300 Volts, 10 Amps



# R95-106A



## 14-Pin Miniature Socket

### Features

- Panel/Surface Mount
- Pressure Clamp Screws
- DPDT or 4PDT
- Screws: 4-40 x 1/4" Steel, Nickel Plated
- Hold down clip supplied with socket, also available separately (R95-001)

### Electrical Rating:

300 Volts, 10 Amps

