

Data & Signal, Plug, 3.5 mm, 2-pole, solder terminal, shielded



### Description

- Solder terminal:  
for cable mounting
- Data and Signal transfer
- Data and Signal Connectors 2-pole, shielded, straight

### References

Alternative: Housing insulated [4802.1210](#)


### Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#)

### Technical Data

Diameter	3.5 mm	Allowable Operation Temp.	-20 °C to 70 °C
Number of Poles	2-pole	Terminal	solder terminal
Ratings DC	1 A / 12VDC	Housing	screened
Ratings AC	1 A / 12VAC	Style	straight
Dielectric Strength	500VDC	Lifetime	10000 Insertions
Insulation Resistance	> 10000 MΩ @ 500VDC		

### Dimensions



### All Variants

Product group	Diameter [mm]	Number of Poles	Terminal	Order Number
Data and Signal Plug/ Sockets	3.5	2-pole	solder terminal	<a href="#">4802.1200</a>

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

**Packaging unit** 100 Pcs

## Mating Outlets/Connectors

## Category / Description



## Data and Signal Plug/Socket Overview complete

Daten & Signal, Socket, 3.5 mm, 2-pole, solder terminal, shielded	4802.2200
Daten & Signal, Socket, 3.5 mm, 2-pole, solder terminal, insulated	4802.2210
Daten & Signal, Socket, 3.5 mm, 2-pole, solder terminals for PCB, shielded	4802.2220
Daten & Signal, Socket, 3.5 mm, 2-pole, solder terminals for PCB, insulated	4802.2230

[Data and Signal Plug/Socket further types to 4802 UK-Stecker, D=3,5mm](#)