

MASTER TL5 Circular

MASTER TL5 Circular 40W/840 1CT

16 mm tube diameter circular fluorescent lamps with a choice of various diameters



Product data

• General Characteristics

Cap-Base	2GX13
Bulb	C-T5 [C-T 16 mm]
Life to 10% fail	8000 hr
Preheat EL,3h	
Life to 50% fail	12000 hr
Preheat EL,3h	
LSF HF Preheat	99 %
2000h Rated,3h	
LSF HF Preheat	99 %
4000h Rated,3h	
LSF HF Preheat	96 %
6000h Rated,3h	
LSF HF Preheat	89 %
8000h Rated,3h	
LSF HF Preheat	50 %
12000h Rated,3h	
LSF HF Preheat	10 %
16000h Rated,3h	
LSF HF Preheat	1 %
20000h Rated,3h	

• Light Technical Characteristics

Colour Code	840 [CCT of 4000K]
Colour Rendering Index	80 (min), 85 (nom), 85 (max) Ra8
Colour Designation	Cool White
Colour Temperature	4000 K
Luminous Flux EL	3300 Lm
25°C, Rated	
Luminous Flux EL	3300 Lm
25°C, Nominal	
Lum Efficacy Rated	83 Lm/W
HF 25°C	
LLMF HF 2000h	91 %
Rated	

LLMF HF 4000h	87 %
Rated	
LLMF HF 6000h	84 %
Rated	
LLMF HF 8000h	81 %
Rated	
LLMF HF 12000h	77 %
Rated	
LLMF HF 16000h	74 %
Rated	
LLMF HF 20000h	72 %
Rated	
Design Temperature	35 C
Chromaticity Coordinate X	380 -
Chromaticity Coordinate Y	380 -

• Electrical Characteristics

Lamp Wattage	40 W
Lamp Wattage EL	39.9 W
25°C, Rated	
Lamp Wattage EL	40 W
25°C, Nominal	
Lamp Voltage EL	126 V
25°C	
Lamp Current EL	0.320 A
25°C	
Dimmable	yes

• Environmental Characteristics

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content	2.5 mg

PHILIPS

MASTER TL5 Circular

Energy consumption 44 kWh
kWh/1000h

• **Measuring Conditions**

Calibration Current 0.320 A
HF Generator Rated Voltage 254 V
Resistor 400 ohm

• **Product Dimensions**


Diameter D 14 (min), 18 (max) mm
Overall Width E 293 (min), 305 (max) mm
Inner Width I 260 (min), 272 (max) mm

• **Product Data**

Order code 642233 25


Full product code 871150064223325
Full product name MASTER TL5 Circular 40W/840 1CT
Order product name MASTER TL5 Circular 40W/840 1CT/10
Pieces per pack 1
Packing configuration 10
Packs per outerbox 10
Bar code on pack - EAN1 8711500642233
Bar code on outerbox - EAN3 8711500642240
Logistic code(s) - 12NC 927965584013
ILCOS code FSCH-40/40/1B-L/P-2GX13-16
Net weight per piece 110.000 gr

Dimensional drawing





MASTER TL5 Circular 40W/840 1CT

Product	D (Min)	D (Max)	E (Min)	E (Max)	I (Min)	I (Max)
TL5-C 40W/840	14	18	293	305	260	272



2GX13

Photometric data



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, October 31
data subject to change