



MASTER TL-D Super 80

MASTER TL-D Super 80 18W/840 1SL

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Product data

• General Characteristics

Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Cap-Base Information	Green Plate
Bulb	T8 [26 mm]
Life to 10% failures EM	12000 hr
Life to 10% fail Preheat EL,3h	17000 hr
Life to 10% fail Nonpreh EL,3h	10000 hr
Life to 50% failures EM	15000 hr
Life to 50% fail Preheat EL,3h	20000 hr
Life to 50% fail Nonpreh EL,3h	12000 hr
LSF EM 2000h Rated, 3h cycle	99 %
LSF EM 4000h Rated, 3h cycle	99 %
LSF EM 6000h Rated, 3h cycle	99 %
LSF EM 8000h Rated, 3h cycle	99 %
LSF EM 12000h Rated,3h cycle	89 %
LSF EM 16000h Rated,3h cycle	33 %
LSF EM 20000h Rated,3h cycle	2 %

• Light Technical Characteristics

Colour Code	840 [CCT of 4000K]
Colour Rendering Index	85 Ra8
Colour Designation	Cool White

Colour Temperature	4000 K
Luminous Flux EM 25°C, Rated	1350 Lm
Luminous Flux EM 25°C, Nominal	1350 Lm
Lum Efficacy Rated EM 25°C	75 Lm/W
Average Luminance EM	1.00 cd/cm ²
LLMF EM 2000h Rated	96 %
LLMF EM 4000h Rated	95 %
LLMF EM 6000h Rated	94 %
LLMF EM 8000h Rated	93 %
LLMF EM 12000h Rated	92 %
LLMF EM 16000h Rated	91 %
LLMF EM 20000h Rated	90 %
Design Temperature	25 C
Chromaticity Coordinate X	380 -
Chromaticity Coordinate Y	380 -

• Electrical Characteristics

Lamp Wattage	18 W
Lamp Wattage EM 25°C, Nominal	18 W
Lamp Wattage EM 25°C, Rated	18.0 W



asimpleswitch.com

PHILIPS

MASTER TL-D Super 80

Lamp Voltage EM 25°C	59 V
Lamp Current EM 25°C	0.360 A
Dimmable	yes

• Environmental Characteristics

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content	2.0 mg
Energy consumption kWh/1000h	22 kWh

• Product Dimensions



Base Face to Base Face A	589.8 (max) mm
Insertion Length B	594.5 (min), 596.9 (max) mm
Overall Length C	604 (max) mm

Diameter D 28 (max) mm

• Product Data

Order code	631718 40
Full product code	871150063171840
Full product name	MASTER TL-D Super 80 18W/840 1SL
Order product name	MASTER TL-D Super 80 18W/840 1SL/25
Pieces per pack	1
Packing configuration	25
Packs per outerbox	25
Bar code on pack - EAN1	8711500631718
Bar code on outerbox - EAN3	8711500631725
Logistic code(s) - 12NC	927920084023
ILCOS code	FD-18/40/1B-E-G13
Net weight per piece	71.000 gr

Dimensional drawing





G13

MASTER TL-D Super 80 18W/840 1SL

Product	A (Max)	B (Min)	B (Max)	C (Max)	D (Max)
TL-D 18W/840	589.8	594.5	596.9	604	28

Photometric data



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, October 31
data subject to change