




TEMPERATURE & PROCESS TECHNOLOGY

## Durable PFA Type K & T Exposed Welded Tip Thermocouples



### About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

### Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

- ◆ Thermocouple types K & T to IEC 584
- ◆ Fast response, welded exposed junction
- ◆ 5 metre long Teflon® PFA insulated twin-twisted lead
- ◆ Durable construction with choice of conductor size, 1/0.315mm solid or 7/0.2mm stranded
- ◆ Miniature plug termination
- ◆ Temperature range -75°C to +250°C
- ◆ Ideal for test & development applications

Thermocouple Type	Conductors Size	Length	Manufactures Part No.	Farnell Order Code
Type K	1/0.315mm	5 m	Z2-K-5.0-MP-1/0.315 PFA TTP+MP	242-0294
Type K	1/0.315mm	10 m	Z2-K-10.0-MP-1/0.315 PFA TTP+MP	242-0263
Type T	1/0.315mm	5 m	Z2-T-5.0-MP-1/0.315 PFA TTP+MP	242-0297
Type T	1/0.315mm	10 m	Z2-T-10.0-MP-1/0.315 PFA TTP+MP	242-0265
Type K	7/0.2mm	5 m	Z2-K-5.0-MP-7/0.2 PFA TTP+MP	242-0295
Type K	7/0.2mm	10 m	Z2-K-10.0-MP-7/0.2 PFA TTP+MP	242-0264
Type T	7/0.2mm	5 m	Z2-T-5.0-MP-7/0.2 PFA TTP+MP	242-0298
Type T	7/0.2mm	10 M	Z2-T-10.0-MP-7/0.2 PFA TTP+MP	242-0266

### Contact Details

Email  
sales@labfacility.com

Website  
www.labfacility.com