

# LMSP1200RI

1200VA  
Intelligent  
Rack-Mount  
UPS



On-board LCD  
Status Display



Servers &  
Data Centres



Desktops  
& PBX systems



Networking &  
Storage



Security &  
Monitoring

The intelligent choice for electrical power protection

Are you looking for a cost-effective, rack-mount UPS with intelligent features for all types of system deployments?

The new range of LMS Power rack-mount UPS devices are ideal for computing, networks, storage and PBX systems of all sizes. The **LMSP1200RI** features a long runtime 1200VA battery with features not found on intelligent UPS at this low price point.

Featuring an advanced microprocessor system for efficient input and output power monitoring, the LMSP1200RI also features a wide input voltage and frequency window, so can be used in a choice of geographical locations, as well as auto-diagnostics, overload protection and auto charging and shutdown when the battery is not under load.

With a low-profile, standard ETSI 19-inch rack-mount design, on-board status LCD display with audible warnings, the LMSP1200RI is your ideal choice for medium to large-scale infrastructure deployment.

## specifications:

1200VA SLA battery chemistry -maintenance free\*

**Supports 110/120 or 220/230/240 volts @ 50/60Hz**

Line interactive technology with modified sine wave support

**Microprocessor monitoring with auto-start diagnostics**

On-load LCD display for 'at a glance' status and variables

**Automatic shutdown and battery conservation support**

Built-in support for telephone and fax systems

**Built-in USB port for Windows(tm) utility monitoring\*\***

Standard (x4) IEC female high density output ports

**User replaceable fuse design to reduce downtimes**

Standard 2U rack-mount, 19-inch design with grab handles



\*actual backup times may vary on systems

\*\* supplied Windows(tm) UPSmart 2000



Copyright 2014 LMS Data  
All trademarks acknowledged E&OE.  
Details subject to change