

RoHS
Compliant

PSG01309



PSG01310



PSG01311



PSG01314



PSG01319



Specifications:

External width	: 20mm
External diameter	: 20mm
Max. cable diameter	: 8mm
Min. cable diameter	: 2mm
Voltage rating	: 60V AC
External length/height	: 66mm
External diameter	: 20mm

Specification Table:

Description	Connector Type	Colour	Length	Number of Poles	Number of Ways	Body Diameter	Part Number
XLR Plug	Free Plug	Black	66mm	3	3	20mm	PSG01309
		Red					PSG01310
		Blue					PSG01311
		Yellow					PSG01312
		Green					PSG01313
		Black		4	4		PSG01314
		Red					PSG01315
		Blue					PSG01316
		Yellow					PSG01317
		Green					PSG01318
		Black		5	5		PSG01319
		Red					PSG01320
		Blue					PSG01321
		Yellow					PSG01322
		Green					PSG01323

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of the Group. © Premier Farnell plc 2012.